



Maximuff Earmuff

29dB - Class 5

PRODUCT DATA SHEET

ITEM CODE: HBE635

Product Overview

- **Materials:** ABS, LDPE, Q-Foam, PP, PVC
- **Dimensions:** height-22cm, length-20cm, width-8.5cm
- **Protection Class:** Class 5
- **SLC80 Rating:** 29dB
- **Country of Origin:** China



Storage

Store in a cool, dry area in the packaging. Do not leave the product in direct sunlight.

Applications

- | | |
|--------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <ul style="list-style-type: none">• Agriculture and farming• Landscaping• Transportation• Building and construction | <ul style="list-style-type: none">• Lightweight manufacturing• Assembly utility• Waste management• General contracting |
|--------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------|

Care/Cleaning Instructions

Cleaning/Maintenance: The cushions should be wiped clean after every use. Wash the cushions & foam pads with mild soap and water, or alcohol swabs, and allow the product to area dry naturally. It is recommended that the product be checked at frequent intervals for cracking and leakage, as these may deteriorate with use. Replace the earmuffs when necessary.

Warranty

Limited lifetime – manufacturing defects

Packaging

Pack: 1 pair

Carton: 20 pairs

Standards and Certification




Class 5 SLC80 29dB Clamp Force:11.1N Mass: 187g

Freq. Hz	125	250	500	1000	2000	4000	8000
Mean	13.0	17.0	25.5	37.2	35.3	40.1	41.4
Std. Deviation	3.1	2.1	2.2	3.3	2.8	3.4	4.4
Mean SD	9.9	14.9	23.3	33.9	32.5	36.7	37.0

Fitting Instructions

1. A cup model hearing protector designed to be used in an over-the-head position.
2. Adjust the ear-cups to their lowest position.
3. Place the cups over the ears.
4. Adjust the headband so that it rests comfortably on the top of the head. Make sure that the cushions are seated firmly on the sides of the head and around the ears.



Guide to Sound Levels

